

Varistar CP Side Panel, Divided, Screw-Fixed



Screw assembly two side panels to close the height of Varistar CP cabinet.

FUNKTIONER

Steel, 1 mm

2 splitted Side panel without grounding kit

SPECIFIKATIONER

Product Type: Cabinet/Rack Panel

Beskyttelsesgrad: IP20

Table 1/2

Katalognummer	Rack Height	Højde	Dybde	Pakke mængde	Farve	Farvekode
21630-060	52U	2450mm	1200mm	2	Black Grey	RAL 7021
21630-052	42U	2000mm	1000mm	2	Black Grey	RAL 7021
21630-055	47U	2200mm	1000mm	2	Black Grey	RAL 7021
21630-054	42U	2000mm	1200mm	2	Black Grey	RAL 7021
21630-056	47U	2200mm	1100mm	2	Black Grey	RAL 7021
21630-057	47U	2200mm	1200mm	2	Black Grey	RAL 7021
21630-058	52U	2450mm	1000mm	2	Black Grey	RAL 7021
21630-059	52U	2450mm	1100mm	2	Black Grey	RAL 7021
21630-053	42U	2000mm	1100mm	2	Black Grey	RAL 7021

Table 2/2

Katalognummer	Finish	Materiale	Type
21630-060	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

Katalognummer	Finish	Materiale	Type
21630-052	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-055	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-054	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-056	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-057	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-058	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-059	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-053	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

YDERLIGERE PRODUKTOPLYSNINGER

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE