

CS480 Swivel Base Bracket Coupling External



CS480 Swivel Base Bracket Coupling External mounts the enclosure directly to horizontal surfaces, enabling 340-degree enclosure rotation. Base mounting hardware is exposed. Maintenance-free bearings.

INDUSTRIE-STANDARDS

IEC 60529, IP66

MERKMALE

Coupling can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket and mounting hardware are included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE