

# Improved nVent CADDY Cat HP J-Hook with Multi-Function Clip



The Improved nVent CADDY Cat HP J-Hook with Multi-Function Clip is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Multi-Function Clip attachment. The Assembly simplifies cable management by offering quick attachment to threaded rod or wire without the need for screws or special tools.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

## ZERTIFIZIERUNGEN



## MERKMALE

Fully adjustable and easy to relocate to accommodate changes once installed

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

## SPEZIFIKATIONEN

Table 1/2

Katalognummer	Artikelnummer	Material	Oberfläche	Durchmesser	Fläche	Kabelkapazität, Cat 5e
CAT16HP4Z34	181217	Stahl, Spring Stahl	Vorverzinkung, nVent CADDY Armour	25 mm	690mm <sup>2</sup>	20
CAT21HP4Z34	181258	Stahl, Spring Stahl	Vorverzinkung, nVent CADDY Armour	33.3 mm	1174mm <sup>2</sup>	50
CAT32HP4Z34	181218	Stahl, Spring Stahl	Vorverzinkung, nVent CADDY Armour	50 mm	2561mm <sup>2</sup>	90

Table 2/2

Katalognummer	Artikelnummer	Kabelkapazität, Cat 6	Kabelkapazität, Cat 6A	Drahtgröße	Stangengröße	Statische Last
CAT16HP4Z34	181217	15	10	3.9 - 4.8 mm <sup>2</sup>	4, 6, 8, 10	130N
CAT21HP4Z34	181258	40	25	3.9 - 4.8 mm <sup>2</sup>	4, 6, 8, 10	130N
CAT32HP4Z34	181218	60	35	3.9 - 4.8 mm <sup>2</sup>	4, 6, 8, 10	130N

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

### Nordamerika

+1.800.753.9221  
Option 1 – Kundendienst  
Option 2 – Technischer Support

### Europa

Niederlande:  
+31 800-0200135  
Frankreich:  
+33 800 901 793

### Europa

Deutschland:  
800 1890272  
Sonstige Länder:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Unser starkes markenportfolio:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

