

Modulschiene, hinten, Typ R-VT, 20 TE

KATALOGNUMMER

34566-720



Combinations of horizontal rails and side panels

		„+“ = can be combined	„+“ = combination not recommended	„+“ = combination not recommended	„+“ = combination not recommended
Rugged rail	Light 1.1	-	+	+	+
	FlexRail 1.1	+	+	+	+
	Heavy 1.1	+	+	+	+
	Rugged 1.1	+	+	+	+
Standard rail	Light 1.1	+	+	-	-
	FlexRail 1.1	+	+	-	-
	Heavy 1.1	+	+	-	-
	Rugged 1.1	+	+	-	-

Light 1.1 FlexRail 1.1 Heavy 1.1 Rugged 1.1

Die Rugged Modulschiene Typ VT, ermöglicht die direkte Montage einer Backplane.

ZERTIFIZIERUNGEN



MERKMALE

Typ R-VT "Rugged"-Modulschiene mit 3-Loch-Befestigung zur Erhöhung der Stabilität

Aluminiumprofil, Oberfläche eloxiert, Kontaktfläche leitfähig

PRODUKTMERKMALE

Breite Gestell: 20HP

Anzahl Verpackungen: 1

Oberfläche: Eloxiert

Länge: 106.68mm

Material: Aluminium

Produktfamilie: EuropacPRO

Produkttyp: Modulschiene

Typ: Robust, VT

Passt zu: Baugruppenträger

ZUSÄTZLICHE PRODUKTDDETAILS

Bitte beachten Sie, dass Lieferungen nur in den jeweils angegebenen LLG (Lieferlosgrößen), LLG z. B. 5 Stück, 10 Stück, 50 Stück usw.) möglich sind. Davon abweichende Bestellmengen (z. B. 2 Stück) werden auf die nächst mögliche lieferbare Menge = Lieferlosgröße (LLG) abgeändert.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE