

# Internal U-Shaped Coupler



## SPECIFICATIONS

**Material:** Steel

Table 1/2

Catalog Number	Article Number	Finish	Strut Type	Length (L)	Screw Included	Screw Diameter (Sc)
ZU405PG	387805	Pregalvanized	A (41 x 41 mm)	250mm	Yes	6
ZUA404	387790	Hot-Dip Galvanized	C (21 x 41 mm)	250mm	No	
ZUA405	387800	Hot-Dip Galvanized	A (41 x 41 mm)	250mm	No	

Table 2/2

Catalog Number	Article Number	Screw Length (L)
ZU405PG	387805	12mm
ZUA404	387790	
ZUA405	387800	

## DIAGRAMS



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

