

Socket Strip, UTE, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



FEATURES

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during fitting

Output via UTE sockets

Horizontal or vertical mounting

Installation height 1 U

In accordance with NFC 61-303

SPECIFICATIONS

- Length:** 438.5mm
- Material:** Aluminum; Polyamide
- Product Type:** Socket Strip

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Function | Package Quantity |
|----------------|-------------|-----------------|------------------|------------|------------------------|------------------|
| 60110-357 | UTE | 6 | No | 230V | Overcurrent Protection | 1 |

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Function | Package Quantity |
|----------------|-------------|-----------------|------------------|------------|------------------------|------------------|
| 60110-356 | UTE | 6 | No | 230V | Overcurrent Protection | 1 |
| 60110-346 | UTE | 8 | No | 230V | | 1 |
| 60110-355 | UTE | 6 | No | 230V | Overcurrent Protection | 1 |
| 60110-348 | UTE | 8 | No | 230V | | 1 |
| 60110-347 | UTE | 8 | No | 230V | | 1 |

Table 2/2

| Catalog Number | Color | Depth | Finish |
|----------------|-------|-------|----------|
| 60110-357 | Red | 44mm | Anodized |
| 60110-356 | Black | 44mm | Anodized |
| 60110-346 | White | 44mm | Anodized |
| 60110-355 | White | 44mm | Anodized |
| 60110-348 | Red | 44mm | Anodized |
| 60110-347 | Black | 44mm | Anodized |

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE