

nVent CADDY Superfix 243 M8, 25–30 mm OD, 3/4" Pipe, 20 DN

CATALOG NUMBER

SXE028



CERTIFICATIONS



FEATURES

Includes easy closing mechanism

Combo head bolt works with slotted, hex, or Phillips drivers

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

PRODUCT ATTRIBUTES

Article Number: 400058

Material: Steel;EPDM-SBR Rubber

Finish: Electro galvanized

Color: Black

Temperature: -50 to 110 °C

Outer Diameter (OD): 26 - 30 mm

Pipe Size: 3/4"

NB/DN: 20

Rod Size (RS): M8

Width (W): 20 mm

Thickness (T): 1.2 mm

Screw Diameter (Sc): 5

Screw Length (L): 25mm

Static Load: 1000N

ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

