

CompacPRO Complete Desktop Case, Unshielded



The pre-configured nVent SCHROFF CompacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frame and sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



FEATURES

Desktop case pre-configured in accordance with IEC 60297-3-101 for 19" components

Aluminum construction ensures robust solution

Side panel with integrated handle function

For backplane mounting with insulation strips

Ventilation slots in rear panel

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

Front and rear identical, depth-symmetrical construction

GND / earthing connections in accordance with (please see catalog page 5.76)

Conforms with DIN EN 62368-1

SPECIFICATIONS

Product Type: Case

Type: Case for 19" Components

Table 1/3

| Catalog Number | Rack Height | Height | Rack Width | Width | Depth | Package Quantity |
|----------------|-------------|---------|------------|-------|-------|------------------|
| 14575-155 | 3U | 147.1mm | 63HP | 364mm | 331mm | 1 |
| 14575-174 | 3U | 147.1mm | 84HP | 471mm | 271mm | 1 |
| 14575-156 | 3U | 147.1mm | 63HP | 364mm | 391mm | 1 |
| 14575-135 | 3U | 147.1mm | 42HP | 257mm | 331mm | 1 |
| 14575-114 | 3U | 147.1mm | 28HP | 186mm | 271mm | 1 |
| 14575-136 | 3U | 147.1mm | 42HP | 257mm | 391mm | 1 |
| 14575-178 | 3U | 147.1mm | 84HP | 471mm | 511mm | 1 |
| 14575-134 | 3U | 147.1mm | 42HP | 257mm | 271mm | 1 |
| 14575-115 | 3U | 147.1mm | 28HP | 186mm | 331mm | 1 |
| 14575-154 | 3U | 147.1mm | 63HP | 364mm | 271mm | 1 |
| 14575-175 | 3U | 147.1mm | 84HP | 471mm | 331mm | 1 |
| 14575-176 | 3U | 147.1mm | 84HP | 471mm | 391mm | 1 |

Table 2/3

| Catalog Number | Usable Height | Usable Width | Front Frame Construction | Cooling Option | Complies With | EMC Shielding |
|----------------|---------------|--------------|--------------------------|----------------|-----------------|---------------|
| 14575-155 | 129.3mm | 326mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-174 | 129.3mm | 432mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-156 | 129.3mm | 326mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-135 | 129.3mm | 219mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-114 | 129.3mm | 148mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-136 | 129.3mm | 219mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-178 | 129.3mm | 432mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-134 | 129.3mm | 219mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-115 | 129.3mm | 148mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-154 | 129.3mm | 326mm | Single Piece | No | IEC 60297-3-103 | No |

| Catalog Number | Usable Height | Usable Width | Front Frame Construction | Cooling Option | Complies With | EMC Shielding |
|----------------|---------------|--------------|--------------------------|----------------|-----------------|---------------|
| 14575-175 | 129.3mm | 432mm | Single Piece | No | IEC 60297-3-103 | No |
| 14575-176 | 129.3mm | 432mm | Single Piece | No | IEC 60297-3-103 | No |

Table 3/3

| Catalog Number | Finish | Material | Protection Rating | Static Load |
|----------------|-------------------------|----------|-------------------|-------------|
| 14575-155 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-174 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-156 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-135 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-114 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-136 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-178 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-134 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-115 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-154 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-175 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |
| 14575-176 | Anodized, Powder Coated | Aluminum | IP20 | 30kg |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE