


nVent CADDY Macrofix Plus LF Low-Friction, 63 mm OD, 2" Pipe, 50 DN, 63 mm Plastic Pipe

CATALOG NUMBER

MPL063



FEATURES

- Includes easy closing mechanism
- Age resistant lining designed specifically for plastic pipe applications
- Low-friction properties allow for expansion, contraction and easy sliding of pipe
- Conforms with Manufacturers Standardization Society (MSS) SP-58 (Type 12)
- Category II noise reduction according to DIN EN ISO 3822-1
- Compliant for sound insulation design according to DIN 4109

PRODUCT ATTRIBUTES

- Article Number: 595042
- Material: Steel;EPDM-SBR Rubber
- Finish: Electrogalvanized
- Color: Green
- Temperature: -50 to 110 °C
- Outer Diameter (OD): 63 mm
- Pipe Size: 2" Min
- NB/DN: 50
- Plastic Pipe Size: 63mm
- Rod Size (RS): M8;M10

Width (W): 30 mm


Thickness (T): 2 mm

Static Load: 1725N

ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

