

# CompacPRO Front/Rear Panel, With Hidden Fixing



The front panel for CompacPRO Case mounts to the frame of the case. The front panel has no visible screws and can be used for front foil.

## CERTIFICATIONS



## FEATURES

Al panel, 2.5 mm

## SPECIFICATIONS

|                        |             |
|------------------------|-------------|
| <b>Material:</b>       | Aluminum    |
| <b>Finish:</b>         | Anodized    |
| <b>Accessory Type:</b> | Front panel |
| <b>Product Type:</b>   | Front Panel |

Table 1/2

| Catalog Number | Rack Height | Height  | Rack Width | Width   | Package Quantity | Front Finish |
|----------------|-------------|---------|------------|---------|------------------|--------------|
| 24575-275      | 4U          | 172.9mm | 84HP       | 452.1mm | 1                | Anodized     |
| 24575-075      | 2U          | 84mm    | 84HP       | 452.1mm | 1                | Anodized     |
| 24575-155      | 3U          | 128.4mm | 63HP       | 345.4mm | 1                | Anodized     |

| Catalog Number | Rack Height | Height  | Rack Width | Width   | Package Quantity | Front Finish |
|----------------|-------------|---------|------------|---------|------------------|--------------|
| 24575-175      | 3U          | 128.4mm | 84HP       | 452.1mm | 1                | Anodized     |
| 24575-455      | 6U          | 261.8mm | 63HP       | 345.4mm | 1                | Anodized     |
| 24575-475      | 6U          | 261.8mm | 84HP       | 452.1mm | 1                | Anodized     |
| 24575-135      | 3U          | 128.4mm | 42HP       | 238.7mm | 1                | Anodized     |
| 24575-255      | 4U          | 172.9mm | 63HP       | 345.4mm | 1                | Anodized     |
| 24575-035      | 2U          | 84mm    | 42HP       | 238.7mm | 1                | Anodized     |
| 24575-235      | 4U          | 172.9mm | 42HP       | 238.7mm | 1                | Anodized     |
| 24575-115      | 3U          | 128.4mm | 28HP       | 167.5mm | 1                | Anodized     |

Table 2/2

| Catalog Number | Rear Finish | Treated Edges | Depth |
|----------------|-------------|---------------|-------|
| 24575-275      | Anodized    | No            | 2.5mm |
| 24575-075      | Anodized    | No            | 2.5mm |
| 24575-155      | Anodized    | No            | 2.5mm |
| 24575-175      | Anodized    | No            | 2.5mm |
| 24575-455      | Anodized    | No            | 2.5mm |
| 24575-475      | Anodized    | No            | 2.5mm |
| 24575-135      | Anodized    | No            | 2.5mm |
| 24575-255      | Anodized    | No            | 2.5mm |
| 24575-035      | Anodized    | No            | 2.5mm |
| 24575-235      | Anodized    | No            | 2.5mm |
| 24575-115      | Anodized    | No            | 2.5mm |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**