

LED Lights for Cabinets

Data Solutions



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICATIONS



FEATURES

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

SPECIFICATIONS

Product Type: Light

Table 1/2

Catalog Number	Accessory Type	Protection Rating	Package Quantity	Color	Finish	Type
57274	Lights	IP20	1	Black	Smooth Matte	Cabinet Light, Terminal Block
57275	Lights	IP20	2		Smooth Matte	Cabinet Light, Magnet
60130-114	Lights	IP20	1		Smooth	Connection Cable

CatalogNumber	AccessoryType	Protection Rating	Package Quantity	Color	Finish	Type
57265	Lights	IP20	1	Black	Smooth Matte	Cabinet Light
57272	Lights	IP20	1	Black	Smooth	Connection Cable
57273	Lights	IP20	1	Black	Smooth	Connection Cable

Table 2/2

Catalog Number	Connection Type	Light Output	Rated Current	Weight	Certifications
57274	Infeed, Trough-Wiring, 2-Pole		16A	0.07kg	RoHS
57275				0.08kg	RoHS
60130-114	Infeed, Trough-Wiring, 2-Pole		10A	0.083kg	RoHS, EAC
57265	Infeed, Trough-Wiring, 2-Pole	550lm		0.24kg	CE, RoHS
57272	Infeed, Trough-Wiring, 2-Pole		10A	0.3kg	RoHS
57273	Infeed, Trough-Wiring, 2-Pole		10A	0.3kg	RoHS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE