We connect and protect

Mobile Base for Open Frame Racks 4-Post, Black, Steel

Data Solutions

CATALOG NUMBER

A19MB600



The Mobile Base for Open-Frame Racks provide stability and mobility to open-frame racks. It has models for both 19-in. 2- and 4-Post Open Frame Racks. This product mounts to the bottom of the racks previously mentioned. It includes four non-locking casters but will also accept standard levelers. Please note, catalog number PMBLM12 must be ordered separately, however the mounting hardware is included.

FEATURES

- The Mobile Base for Open-Frame Racks provide stability and mobility to open-frame racks
- It has models for both 19-in. 2- and 4-Post Open Frame Racks
- This product mounts to the bottom of the racks previously mentioned. It includes four non-locking casters but will also accept standard levelers
- Please note, catalog number PMBLM12 must be ordered separately, however the mounting hardware is included

PRODUCT ATTRIBUTES

- Article Number: 13772
- Material: Mild Steel
- Finish: Powder Coated
- Color: Jet Black
- Color Code: RAL 9005
- Thickness: 2.66mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.