

Rack- and Panel-Mount PDU 18 Rec 15A, 48-in length, Black, Steel

Data Solutions

CATALOG NUMBER

DP1N481815



The Rack- and Panel-Mount PDUs not only provide convenient, reliable power to equipment mounted in cabinets or on open frame racks, but they can also be configured to meet a wide range of design specifications. These PDU's are a basic, lower-cost solution that provide great value.

INDUSTRY STANDARDS

UL/cUL 60950 listed

UL 1449 (Surge protector models only)

EIA 310-D (19-in. rack-mount models only)

FEATURES

Finish: Textured

Color: Black

Length: 1219mm

Surge Protection: No

Electrical Load Rating: 15A

Voltage AC: 120V

Socket Quantity: 18

Socket Type: NEMA 5-15R

Plug Type: NEMA 5-15P

ADDITIONAL PRODUCT DETAILS

Contact nVent HOFFMAN for custom modifications and non-standard offerings.

Isolate circuits on dual circuit models with separate circuit breakers.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

