

Rack-Mountable Tray 19-inch

Data Solutions

Fan trays enhance the natural convection airflow within a cabinet when installed with other 19-inch rack-mount equipment.



FEATURES

Fan trays available with either three or six 4-inch fans

Includes 72-inch (1829-mm) power cord with IEC 320 standard power socket

Power cord plugs into standard 115 VAC outlet

Lighted rocker switch provides on-off control and indicates when fans are on

SPECIFICATIONS

- Color:** Jet Black
- Material:** Mild Steel
- Finish:** Powder Coated
- Color Code:** RAL 9005

Table 1/2

| Catalog Number | Article Number | Height | Width | Fan Quantity | Input Voltage AC | Depth |
|----------------|----------------|--------|-------|--------------|------------------|-------|
| A19FT6B | 13856 | 42mm | 483mm | 6 | 100 – 120V | 329mm |
| A19FT3B | 13855 | 42mm | 483mm | 3 | 100 – 120V | 206mm |

Table 2/2

| Catalog Number | Article Number | Nominal Watts | Temperature | Thickness |
|----------------|----------------|---------------|-------------|-----------|
| A19FT6B | 13856 | 90W | 70°C max | 1.52mm |

| Catalog Number | Article Number | Nominal Watts | Temperature | Thickness |
|----------------|----------------|---------------|-------------|-----------|
| A19FT3B | 13855 | 45W | 70°C max | 1.52mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE