

Solid Copper Ground Rod, Pointed



CERTIFICATIONS



FEATURES

Solid copper ground rods made of high conductive hard drawn bare copper

SPECIFICATIONS

Tensile Strength: 290 MPa Min
Material: Copper

Table 1/1

| Catalog Number | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual (Ø) | Length (L) | Unit Weight | Certifications |
|----------------|------------------------------|---------------------------------|------------|-------------|----------------|
| LPC700 | 1/2" | 12.7 mm | 2.44mm | 2.76 kg | UL |
| LPC702 | 1/2" | 12.7 mm | 3.05mm | 3.44 kg | UL, cUL |
| LPC706 | 5/8" | 15.9 mm | 3.05mm | 5.35 kg | UL, cUL |
| LPC704 | 5/8" | 15.9 mm | 2.44mm | 4.29 kg | UL |
| LPC711 | 3/4" | 19.1 mm | 3.05mm | 7.7 kg | cUL, UL |

ADDITIONAL PRODUCT DETAILS

Due to the inherent softness of the copper material, special consideration should be given when driving this product into the soil.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE