


ComLine OSP Wall-Mount Rack Angles



The ComLine OSP Wall-Mount Rack Angles are used to mount 19in rack equipment inside the cabinet. They are grounded to the cabinet body through the mounting bolts. Please note the square mounting holes meet EIA standard and each package includes one pair.

FEATURES

The ComLine OSP Wall-Mount Rack Angles are used to mount 19in rack equipment inside the cabinet

They are grounded to the cabinet body through the mounting bolts

Please note the square mounting holes meet EIA standard and each package includes one pair

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Thickness	Rack Units
ERA192312S	17042	Mild Steel	Zinc Plated	2.66mm	25U
ERA196S	17037	Mild Steel	Zinc Plated	2.66mm	12U
ERA199S	17038	Mild Steel	Zinc Plated	2.66mm	18U
ERA19239S	17041	Mild Steel	Zinc Plated	2.66mm	18U

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE