

CS480 Angle Coupling



CS480 Angle Coupling mounts between a tube and the enclosure to provide tilt option for the machine operator. Rigid flange coupling with 15-degree angle of inclination for attaching enclosure.

INDUSTRY STANDARDS

IEC 60529, IP66

FEATURES

Enclosure is mounted at a 15-degree incline angle

Gasket and mounting hardware are included

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
CCSS48AC15	42479	80mm	70mm	70mm	Stainless Steel 304	Brushed

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE