

# PropacPRO Complete Desktop Case, Shielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. The case includes EMC shielding as standard.

## CERTIFICATIONS



## FEATURES

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Shielded

Ventilation slots in base plate

Rear panel with vent slots

IP 20 in accordance with IEC 60529

Conforms with DIN EN 62368-1

## SPECIFICATIONS

- Static Load:** 25kg
- Product Type:** Case
- Type:** Case for 19" Components
- Product Family:** PropacPRO
- EMC Shielding:** Yes

Table 1/3

Catalog Number	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
----------------	-------------	------------	-------	------------------	---------------	--------------

24576-122	6U	84HP	446mm	1	245.7mm	432mm
24576-105	3U	42HP	386mm	1	112.3mm	219mm
24576-102	3U	28HP	326mm	1	112.3mm	148mm
24576-110	3U	84HP	326mm	1	112.3mm	432mm
24576-111	3U	84HP	386mm	1	112.3mm	432mm
24576-121	6U	84HP	326mm	1	245.7mm	432mm
24576-104	3U	42HP	326mm	1	112.3mm	219mm
24576-106	3U	63HP	266mm	1	112.3mm	326mm
24576-109	3U	84HP	266mm	1	112.3mm	432mm
24576-112	3U	84HP	446mm	1	112.3mm	432mm
24576-113	3U	84HP	506mm	1	112.3mm	432mm
24576-103	3U	42HP	266mm	1	112.3mm	219mm
24576-107	3U	63HP	326mm	1	112.3mm	326mm
24576-101	3U	28HP	266mm	1	112.3mm	148mm
24576-108	3U	63HP	386mm	1	112.3mm	326mm

Table 2/3

Catalog Number	Front Frame Construction	Cooling Option	Complies With	Finish	Height	Material
24576-122	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	289mm	Aluminum
24576-105	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-102	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-110	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-111	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-121	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	289mm	Aluminum
24576-104	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-106	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-109	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-112	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum

Catalog Number	Front Frame Construction	Cooling Option	Complies With	Finish	Height	Material
24576-113	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-103	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-107	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-101	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-108	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum

Table 3/3

Catalog Number	Protection Rating	Width
24576-122	IP20	470.3mm
24576-105	IP20	257mm
24576-102	IP20	185.9mm
24576-110	IP20	470.3mm
24576-111	IP20	470.3mm
24576-121	IP20	470.3mm
24576-104	IP20	257mm
24576-106	IP20	363.7mm
24576-109	IP20	470.3mm
24576-112	IP20	470.3mm
24576-113	IP20	470.3mm
24576-103	IP20	257mm
24576-107	IP20	363.7mm
24576-101	IP20	185.9mm
24576-108	IP20	363.7mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**