

# CompacPRO Tip-Up Handle

Tip-up carrying handle.



## CERTIFICATIONS



## FEATURES

Load-carrying capacity 20 kg

Carrying bar adjustable in increments of 30° by push button

With powder-coated carrying bar

The handle enable a user to have a better view to the front side of the case in case of desktop usage

## SPECIFICATIONS

**Works With:** Cases  
**Product Family:** CompacPRO  
**Product Type:** Handle

Table 1/1

| Catalog Number | Rack Width | Package Quantity | Handle Type   | Length | Material             |
|----------------|------------|------------------|---------------|--------|----------------------|
| 24575-038      | 42HP       | 1                | Tip-up Handle | 180mm  | Aluminum, Zinc Alloy |
| 24575-178      | 84HP       | 1                | Tip-up Handle | 180mm  | Aluminum, Zinc Alloy |

| Catalog Number | Rack Width | Package Quantity | Handle Type   | Length | Material             |
|----------------|------------|------------------|---------------|--------|----------------------|
| 24575-158      | 63HP       | 1                | Tip-up Handle | 180mm  | Aluminum, Zinc Alloy |
| 24575-138      | 42HP       | 1                | Tip-up Handle | 180mm  | Aluminum, Zinc Alloy |
| 24575-118      | 28HP       | 1                | Tip-up Handle | 180mm  | Aluminum, Zinc Alloy |
| 24575-078      | 84HP       | 1                | Tip-up Handle | 180mm  | Aluminum, Zinc Alloy |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**