

Drop-In Anchor



FEATURES

Internal thread provides easy removal and serviceability

Installs flush or below the base surface

Suitable for redundant non-structural systems on cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire

SPECIFICATIONS

Table 1/1

| Catalog Number | Material | Finish | Hole Size (HS) | Length (L) |
|----------------|----------|-------------------|----------------|------------|
| CA0037EG | Steel | Electrogalvanized | 9.5 mm | 39.7mm |


Characteristic Axial Loads from ETA 14-0135

| Part Number | Cracked Concrete C20/25 | Non-Cracked Concrete C20/25 | Standard Embedment Depth |
|-------------|-------------------------|-----------------------------|--------------------------|
| CAM6030 | - | 2.50 kN | 25 mm |
| CAM8030 | - | 3.30 kN | 30 mm |
| CAM10040 | - | 4.40 kN | 40 mm |
| CAM12050 | - | 6.10 kN | 50 mm |
| CAM8030S6 | - | - | - |
| CAM10040S6 | - | - | - |

Characteristic Axial Loads from ETA 14-0068 - for redundant non-structural systems

| Part Number | Cracked Concrete C20/25 | Non-Cracked Concrete C20/25 | Standard Embedment Depth |
|-------------|-------------------------|-----------------------------|--------------------------|
| CAM6030 | 0.80 kN | 0.80 kN | 25 mm |
| CAM8030 | 1.20 kN | 1.20 kN | 30 mm |
| CAM10040 | 1.70 kN | 1.70 kN | 40 mm |
| CAM12050 | 2.60 kN | 2.60 kN | 50 mm |
| CAM8030S6 | 1.20 kN | 1.20 kN | 25 mm |
| CAM10040S6 | 1.70 kN | 1.70 kN | 40 mm |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

