

Drop Threaded Rod with Shot-Fire Bracket



CERTIFICATIONS



FEATURES

Quickly and easily attaches to concrete, steel or composite metal decking

Integrated pin installs easily using powder-actuated or single-shot gas-actuated tools

Works with most standard nVent CADDY spring steel fasteners designed for rod attachments

Rod is rigid and does not require secondary attachment to ceiling grid per NEC 300.11

Stocked inventory - available when you need it

Includes pre-assembled end-cap

Specialized packaging simplifies material handling and minimizes sorting

Rods are ready to install out of the box

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Length (L)	A	Static Load
DR4TSF48	1219mm	33 mm	420N

Catalog Number	Length (L)	A	Static Load
DR4TSF36	914mm	33 mm	420N
DR4TSF60	1524mm	33 mm	420N
DR4TSF40	1016mm	33 mm	420N
DR4TSF24	610mm	33 mm	420N
DR4TSF72	1829mm	33 mm	420N
DR4TSF12	305mm	33 mm	420N

ADDITIONAL PRODUCT DETAILS

Uses Powers Fasteners, Inc. part number 50378.

Static load was established based on a 1-1/8" (28.6 mm) embedment depth and 3,000 psi (20.68 Mpa) normal-weight concrete. For variations in embedment and material please consult www.powers.com.


Pre-assembled drive pin from Powers Fasteners, Inc. works with Powers® C4CZ, Simpson® GCN-MEPKT, SPIT® P1000, P200, P2201, P3500 / PA3500, P35s, P45, P60, P7201, Sniper; Ramset® 721, Cobra, D45 / D60 / D60L, M70, SA270, T3SS, TS750P, TS60P, Viper; Hilti® DX35, DX350 / DX351 / DX36M, DX100 / DX200, DX460, DXA40, DXA41, DXE72 / DX400; Würth® Diva-1, BST-1, BST-2 or equivalent nailers.

For shot-fired supports in seismic design category D, E, or F, maximum load is the lesser of 90 lb (400 N) or the published load.

Exempt from seismic design when supporting conduits less than 2-1/2" (64 mm) trade size, regardless of Ip.

Refer to DeWalt Engineered by Powers Ceiling Clip Assembly ICC-ES Evaluation Report ESR-2024 for the allowable load ratings in various substrate material and embedment depths.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

