

# 511 nVent CADDY EZ Riser for Copper Tube, 1 1/2" Pipe, 1 5/8" OD

## CATALOG NUMBER

**5110150CP**



The 511 nVent CADDY EZ Riser for Copper Tubes is a quick-closing pipe clamp, ideal for supporting vertical copper tubes where space is available. Ready-to-use out of the box, this solution has slotted holes to simplify assembly and eliminate loose hardware. Due to the serrated washer-head design, installers can easily assemble the EZ Riser for Copper Tube with just a single tool.

## FEATURES

Only one tool needed to tighten due to serrated wash-heads

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

## PRODUCT ATTRIBUTES

Material: Steel

Finish: Copper Electroplated

Pipe Size: 1 1/2"

Outer Diameter (OD): 41.3 mm

Hole Size (HS): 11.1 mm

Length (L): 38.25mm

A: 241.3 mm

B: 31.75 mm

Screw Length (L): 38.2mm

Static Load: 667N

## ADDITIONAL PRODUCT DETAILS

Clamp is fitted for copper tube and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

