

Threaded Bridle Ring



CERTIFICATIONS



FEATURES

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Diameter	Screw Diameter	Screw Type	Screw Length	Ultimate Static Load	Certifications
4BRT64	100 mm	6	Metal	19mm	220N	UL, cUL
4BRT32	50 mm	6	Metal	19mm	220N	cUL, UL
4BRT20	31.8 mm	6	Metal	19mm	220N	UL, cUL
2BRT8	12.7 mm	4.8	Metal	14.3mm	220N	cUL, UL
2BRT32	50.8 mm	4.8	Metal	14.3mm	220N	cUL, UL
2BRT20	31.8 mm	4.8	Metal	14.3mm	220N	cUL, UL
4BRT20WS	31.8 mm	14	Wood	19.1mm	220N	cUL, UL

CatalogNumber	Diameter	ScrewDiameter	Screw Type	Screw Length	Ultimate Static Load	Certifications
4BRT32WS	50 mm	14	Wood	19mm	220N	cUL, ITB, UL

ADDITIONAL PRODUCT DETAILS

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

