

nVent CADDY Cablecat J-Hook with Shot-Fire Bracket, 3/4" dia

Data Solutions

CATALOG NUMBER

CAT12SF



FEATURES

Cost effective alternative to expensive cable tray

Galvanized finish on J-Hooks provide smoother cable pull and greater corrosion resistance

Complete with shot-fire bracket and pre-assembled drive pin from DEWALT®

Quickly and easily attaches to concrete, steel or composite metal decking

Integrated pin installs easily using powder-actuated or single-shot gas-actuated tools

ICC-ES ESR-2024 evaluation report available for drive pin from DEWALT®

PRODUCT ATTRIBUTES

Material: Steel

Finish: Electrogalvanized; Pregalvanized

Diameter (Ø): 50.8mm

Height (H): 103.2mm


A: 33mm

ADDITIONAL PRODUCT DETAILS

Uses Powers Fasteners, Inc. part number 50032.

Pre-assembled drive pin from Powers Fasteners, Inc. works with Powers® C4CZ, Simpson® GCN-MEPKT, SPIT® P1000, P200, P2201, P3500 / PA3500, P35s, P45, P60, P7201, Sniper; Ramset® 721, Cobra, D45 / D60 / D60L, M70, SA270, T3SS, TS750P, TS60P, Viper; Hilti® DX35, DX350 / DX351 / DX36M, DX100 / DX200, DX460, DXA40, DXA41, DXE72 / DX400; Würth® Diva-1, BST-1, BST-2 or equivalent nailers.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE