


Non-Insulated Solid Conductor



FEATURES

Solid cable for a variety of applications

Available in smaller spool sizes for convenience

LPA and LPC parts are used for lightning protection system downconductor or grounding applications

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Conductor Size	Cross Section	Diameter (Ø)	Length (L)
LPA141CTO	Aluminum	Bare	#4 Solid	21.15mm ²	5.08 mm	
LPA141500	Aluminum	Bare	#4 Solid	21.15mm ²	5.08 mm	152.4m
LPA141250	Aluminum	Bare	#4 Solid	21.15mm ²	5.08 mm	76.2m
LPC151CTO	Copper	Bare	#6 Solid	13.29mm ²	4 mm	
A809A06F100	Copper	Bare	#4 Solid	21.2mm ²	5.2 mm	30.5m
LPC154CTO	Copper	Bare	#2 Solid	33.62mm ²	8.3 mm	
LPC154LCTO	Copper	Tinned	#2 Solid	33.62mm ²	8.3 mm	

Table 2/2

Catalog Number	Unit Weight
LPA141CTO	0.02 kg
LPA141500	0.02 kg
LPA141250	0.02 kg
LPC151CTO	0.04 kg


Catalog Number	Unit Weight
A809A06F100	0.06 kg
LPC154CTO	0.09 kg
LPC154LCTO	0.09 kg

ADDITIONAL PRODUCT DETAILS

Unit weight is per foot (0.3048 m).

Cut-to-order (CTO) lengths are available for an additional charge.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE