

ProLine G2 Leveler Kit



The Post-type Leveler Kit allows for height adjustment at the enclosure corners to account for uneven floors. Levelers thread into the frame corners, and can be used with a bottom-mounted Gland Plate or a 0-mm Solid Base; they may also be affixed to the corner blocks of the standard Plinth Base. Levelers are plated for indoor use, and are rated to 3000 lbs. (1361 kg).

FEATURES

The Mobile Base Leveling Kit allows for height adjustments at the corners of the Mobile Base to account for uneven floors

Levelers are plated for indoor use, and are rated to 3000 lbs. (1361 kg)

SPECIFICATIONS

Finish: Plated

Table 1/1

Catalog Number	Article Number	Material
P2ALK	36156	Mild Steel
P2ALKMB	36206	Mild Steel

ADDITIONAL PRODUCT DETAILS

Note: the non-locking casters of the Mobile Base have a load bearing capacity of 1000 lbs. (453.6 kg): exercise caution if disengaging the levelers.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE