

Single Temperature and Humidity Sensor

CATALOG NUMBER

EA9103

Single Temperature and Humidity Probe Sensor for Enlogic.



FEATURES

Single Temperature and Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For Enlogic

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +/- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +/- 5 %

PRODUCT ATTRIBUTES

Product Type: Sensor

Works With: RackPower

Height: 270mm

Package Quantity: 1

Plug Type: RJ45

Product Family: Enlogic

Removable Input Cable: No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE