

# Nonmetallic Ventilator



This nonmetallic ventilator provides rainproof ventilation for metallic and non-metallic enclosures.

## FEATURES

Proper installation will provide rainproof ventilation but will not meet Type 4 or 12 requirements

Kit includes mounting hardware and instructions

Supplied screws are 13-mm (.515-inch) long and some applications may require longer screws.

## SPECIFICATIONS

- Color:** Light Gray
- Material:** Plastic
- Color Code:** RAL 7035
- Finish:** Smooth Matte

Table 1/1

Catalog Number	Article Number	Height	Width	Depth
ANMV6	50400	69mm	51mm	21mm
ANMV3	50410	27mm	25mm	22mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**