

# Compact LED-Light 550LM Motion Sensor

## Data Solutions

### CATALOG NUMBER

**57265**



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

### CERTIFICATIONS



### FEATURES

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

### PRODUCT ATTRIBUTES

Input Voltage AC: 230V max

Accessory Type: Lights

Input Voltage DC: 24V max

Protection Rating: IP20

Length: 396mm

Package Quantity: 1

Color: Black

Depth: 40mm

Finish: Smooth Matte

Material: Plastic

Product Type: Light

Type: Cabinet Light

Width: 33mm

Color Temperature: 5300K

Connection Type: Infeed; Trough-Wiring; 2-Pole

Light Output: 550lm

Nominal Voltage: 230V

Operating Temperature: -20 to 55°C

Weight: 0.24kg

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE