

Pipe Thread Connector



FEATURES

Connect threaded pipe to PX pipe clamps


Female-to-female connector

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Gewinde (G)	Height (H)
PTC050EG	578730	Steel	Electrogalvanized	1/2"	18 mm
PTC050S6	578800	Stainless Steel 316 (EN 1.4401)		1/2"	18 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

