

19" Front Panel, Vented, 3 U, 2.5 mm, Al, Anodized

Data Solutions

CATALOG NUMBER

30702-049



Vented front panels allows heat dissipation through holes.

CERTIFICATIONS



FEATURES

Vented front panels (Aluminum) allows heat dissipation

PRODUCT ATTRIBUTES

Rack Height: 3U

Accessory Type: Front panel

Finish: Anodized

Mounting: Screw-on Front

Package Quantity: 1

Front Finish: Anodized

Rear Finish: Anodized

Treated Edges: Yes

EMC Shielding: No

Height (H): 132.5mm

Material: Aluminum

Product Type: Front Panel

Rack Width: 95HP

Type: 19" Front Panel

Width (W): 483mm

Net Weight: 0.364kg

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY **ERICO** **HOFFMAN** **ILSCO** **SCHROFF** **TRACHTE**