

Varistar CP Cabeling Rack

Data Solutions



Welded steel frame for high static load requirements.
Prepared for high cable densities and 19" integration.

FEATURES

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

SPECIFICATIONS

Product Type: Rack

Material: Steel

Frame Material: Steel

Table 1/3

| Catalog Number | Rack Height | Cladding Material | Frame Color | Height | Frame Color Code | Cladding Color |
|----------------|-------------|-------------------|-------------|--------|------------------|----------------|
| 10630-027 | 42U | Steel | Black Grey | 2000mm | RAL 7021 | Black Grey |
| 10630-028 | 42U | Steel | Black Grey | 2000mm | RAL 7021 | Black Grey |

Table 2/3

| Catalog Number | Width | Depth | Static Load | Cladding Color Code | Package Quantity | Dynamic Load |
|----------------|-------|--------|-------------|---------------------|------------------|--------------|
| 10630-027 | 800mm | 1200mm | 1600kg | RAL 7021 | 1 | 1000kgf |
| 10630-028 | 800mm | 1200mm | 1600kg | RAL 7021 | 1 | 1000kgf |

Table 3/3

| Catalog Number | Finish |
|----------------|---------------|
| 10630-027 | Powder Coated |
| 10630-028 | Powder Coated |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE