

# Plain Bridle Ring



## CERTIFICATIONS



## SPECIFICATIONS

**Finish:** Electrogalvanized  
**Material:** Steel

Table 1/1			
Catalog Number	Diameter	Wire Size	Ultimate Static Load
2BR8	12.7 mm	5 mm	220N
2BR12	19.1 mm	5 mm	220N
2BR20	31.8 mm	5 mm	220N
2BR32	50.8 mm	5 mm	220N

## ADDITIONAL PRODUCT DETAILS

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

