


Rack-Mount Steel Shelf Vented, 19.00x22.00, Black, Steel

Data Solutions

CATALOG NUMBER

EMSV1922



The Open-Frame Rack-Mount Steel Shelf mounts to the front of the rack and is ideal for holding non-19-in. rack-mount equipment. It is available with or without vents. Please note the load rating is 100 lb. (45.4 kg).

FEATURES

The Open-Frame Rack-Mount Steel Shelf mounts to the front of the rack and is ideal for holding non-19-in. rack-mount equipment

It is available with or without vents. Please note the load rating is 100 lb. (45.4 kg)

PRODUCT ATTRIBUTES

Article Number: 13268

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 1.52mm

Height: 133mm

Width: 482mm

Depth: 559mm

Rack Units: 3U

Type: Vented

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE