We connect and protect

# AccessPlus Double-Hinge Type 1 solid, 48.00x24.00x25.00, Black, Steel

## Data Solutions

### CATALOG NUMBER

**EWMS482425**

AccessPlus Cabinets provide security, equipment access, cooling and support for network and other 19-inch rack-mount equipment. The cabinet has three components: front door, center section and wall section.

### INDUSTRY STANDARDS

UL 2416; Type 1; File No. E230874

cUL Listed per CSA C22.2 No. 182.4; File No. E230874

EIA 310-D

NEMA/EEMAC Type 1

EIC 60529 IP20

Per BICSI TDMM Tenth edition, Chapter 7, Telecommunication Enclosures (TE)

### FEATURES

| |
|---|
| Double-hinged for easy equipment access; center section provides 19-in. rack mounting per EIA universal spacing and is accessed through the front door or swing the center section away from the wall section for rear access |
| Front door has either a solid steel or hardened, tinted safety-glass window door for superior scratch resistance |
| Center section easily removed from rear section; tool-less one person installation possible |
| Self-grounding, plated steel rack angles fully adjustable within center section |
| Wall section provides cable entry and cable management with knockouts or gland plates |
| Gland plate model provides easy retrofit and fast installation and allows for pre-terminated cables or pre-wired patch panels; no need to re-terminate and test |
| Self-locking center-to-wall section latches in two locations |
| Front access to all latches (no exposed side latches); cabinet can be installed tightly in corners |
| Vented sides provide cross flow ventilation to improve heat dissipation |
| Vertical cable manager included in 28-in.-wide models |
| One set of plated, self-grounding, tapped 10-32 rack angles per EIA universal spacing standards, which can be adjusted front to-back, is provided with each center section of the cabinet; additional tapped- or square-hole rack angles can be |

added to the cabinet to provide additional mounting

## PRODUCT ATTRIBUTES

Article Number: 17878

Height: 1220mm

Width: 600mm

Depth: 637mm

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 1.9mm

Rack Units: 26U

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.