Neutral Bar for TD Distribution Blocks, 125 A IEC

Data Solutions

CATALOG NUMBER

NB-125A

CERTIFICATIONS

RoHS

FEATURES

- Attaches to four pole distribution blocks for increased wire capacity
- Direct electrical connection
- Strong mechanical assembly
- Transparent protection cover
- Halogen free
- RoHS compliant
- Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

PRODUCT ATTRIBUTES

Article Number: 563841

Max Current Rating, IEC: 125A
Short Term Withstand Current (Icw) 1s: 4.5kA
Peak Short Circuit Current (Ipk): 30kA
Line Side Number of Connections: 3
Line Side Compact Stranded Wire Size: 10 - 25 mm²
Line Side Stranded Wire Size - Ferrule: 6 – 16mm²
Load Side Number of Connections: 9
Load Side Compact Stranded Wire Size: 2,5 - 6 mm²
Load Side Stranded Wire Size - Ferrule: 1,5 – 6 mm²
Depth (D): 37.4mm
Height (H): 34.3mm
Width (W): 142mm
Unit Weight: 0.17kg
For Use With: TD-100-125AL (563830); TD-100-125ALL (563840)
Flammability Rating: UL® 94V-0
Complies With: IEC® 60947-7-1

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.