

# Heavy Duty Pipe Clamp, Painted, Red Oxide, 110–115 mm OD, 4" Pipe, 100 DN

## CATALOG NUMBER

**SSG115R0**



## FEATURES

For high static requirements in industrial construction

Suitable for fix point applications

## PRODUCT ATTRIBUTES

Article Number: 574680

Material: Steel

Finish: Painted;Red Oxide

Outer Diameter (OD): 110 - 115 mm

Pipe Size: 4"

NB/DN: 100

Hole Size (HS): 18 mm

Screw Diameter (Sc): 16 mm

Screw Length (L): 60mm

Static Load: 2900N

Width (W): 50 mm

Thickness (T): 6 mm

A: 167 mm

ADDITIONAL PRODUCT DETAILS

Static load refers to a complete set of Heavy Duty Pipe Clamps held in place with indicated screws per ISO 4014 and corresponding hex nuts per ISO 4032 (for further information, please refer to Standard SSG 7075E).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

