

Digital Contact Sensor (Output) for Guardian Management Gateway

CATALOG NUMBER

21070-124



External sensor monitoring digital inputs/outputs with 2 RJ45 connectors. Up to 16 sensors can be daisy chained over patch cables and connected to one Guardian Management Port.

FEATURES

External sensor for the Guardian Management Gateway

A port is capable of monitoring up to 16 sensor devices with a total cable length of 40 meters

If an nVent SCHROFF Guardian sensor is connected, it appears in the web interface with type and serial number

Metal housing

Easy Mounting

2 x RJ 45 connection

Easy daisy chain with CAT6 patch cable (or higher shielding)

PRODUCT ATTRIBUTES

Product Type: Sensor

Type: Digital Contact

Works With: Guardian Management Gateway

Gross Weight: 0.108kg

Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE