

Varistar CP Frame



Varistar CP welded frame is available for static load requirements and can be integrated with 19", ETSI or mounting plate. Additionally, castors can be added to the frame if needed.

However, if you require castors for your application, you might want to consider a mobile frame that already includes castors.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

SPECIFICATIONS

Static Load: 1600kg
Product Type: Cabinet/Rack Frame
Material: Steel

Table 1/2

| Catalog Number | Rack Height | Height | Width | Depth | Package Quantity | Color |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-118 | 47U | 2200mm | 800mm | 800mm | 1 | Black Grey |
| 20630-067 | 24U | 1200mm | 600mm | 900mm | 1 | Black Grey |
| 20630-091 | 38U | 1800mm | 600mm | 600mm | 1 | Black Grey |
| 20630-120 | 47U | 2200mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-084 | 33U | 1600mm | 600mm | 800mm | 1 | Black Grey |
| 20630-126 | 52U | 2450mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-092 | 38U | 1800mm | 600mm | 800mm | 1 | Black Grey |
| 20630-119 | 47U | 2200mm | 800mm | 900mm | 1 | Black Grey |
| 20630-125 | 52U | 2450mm | 600mm | 1200mm | 1 | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Depth | Package Quantity | Color |
|----------------------|--------------------|---------------|--------------|--------------|-------------------------|--------------|
| 20630-075 | 29U | 1400mm | 600mm | 600mm | 1 | Black Grey |
| 20630-089 | 33U | 1600mm | 800mm | 900mm | 1 | Black Grey |
| 20630-072 | 24U | 1200mm | 800mm | 800mm | 1 | Black Grey |
| 20630-117 | 47U | 2200mm | 800mm | 600mm | 1 | Black Grey |
| 20630-095 | 38U | 1800mm | 800mm | 600mm | 1 | Black Grey |
| 20630-128 | 52U | 2450mm | 800mm | 1200mm | 1 | Black Grey |
| 20630-114 | 47U | 2200mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-096 | 38U | 1800mm | 800mm | 800mm | 1 | Black Grey |
| 20630-124 | 52U | 2450mm | 600mm | 1100mm | 1 | Black Grey |
| 20630-079 | 29U | 1400mm | 800mm | 600mm | 1 | Black Grey |
| 20630-093 | 38U | 1800mm | 600mm | 900mm | 1 | Black Grey |
| 20630-087 | 33U | 1600mm | 800mm | 600mm | 1 | Black Grey |
| 20630-074 | 24U | 1200mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-094 | 38U | 1800mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-077 | 29U | 1400mm | 600mm | 900mm | 1 | Black Grey |
| 20630-073 | 24U | 1200mm | 800mm | 900mm | 1 | Black Grey |
| 20630-076 | 29U | 1400mm | 600mm | 800mm | 1 | Black Grey |
| 20630-122 | 47U | 2200mm | 800mm | 1200mm | 1 | Black Grey |
| 20630-101 | 42U | 2000mm | 600mm | 900mm | 1 | Black Grey |
| 20630-097 | 38U | 1800mm | 800mm | 900mm | 1 | Black Grey |
| 20630-090 | 33U | 1600mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-088 | 33U | 1600mm | 800mm | 800mm | 1 | Black Grey |
| 20630-098 | 38U | 1800mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-068 | 24U | 1200mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-078 | 29U | 1400mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-123 | 52U | 2450mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-112 | 47U | 2200mm | 600mm | 800mm | 1 | Black Grey |
| 20630-102 | 42U | 2000mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-085 | 33U | 1600mm | 600mm | 900mm | 1 | Black Grey |
| 20630-065 | 24U | 1200mm | 600mm | 600mm | 1 | Black Grey |
| 20630-110 | 42U | 2000mm | 800mm | 1200mm | 1 | Black Grey |
| 20630-083 | 33U | 1600mm | 600mm | 600mm | 1 | Black Grey |
| 20630-105 | 42U | 2000mm | 800mm | 600mm | 1 | Black Grey |
| 20630-109 | 42U | 2000mm | 800mm | 1100mm | 1 | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Depth | Package Quantity | Color |
|---------------|-------------|--------|-------|--------|------------------|------------|
| 20630-082 | 29U | 1400mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-106 | 42U | 2000mm | 800mm | 800mm | 1 | Black Grey |
| 20630-100 | 42U | 2000mm | 600mm | 800mm | 1 | Black Grey |
| 20630-086 | 33U | 1600mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-107 | 42U | 2000mm | 800mm | 900mm | 1 | Black Grey |
| 20630-066 | 24U | 1200mm | 600mm | 800mm | 1 | Black Grey |
| 20630-104 | 42U | 2000mm | 600mm | 1200mm | 1 | Black Grey |
| 20630-080 | 29U | 1400mm | 800mm | 800mm | 1 | Black Grey |
| 20630-108 | 42U | 2000mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-081 | 29U | 1400mm | 800mm | 900mm | 1 | Black Grey |
| 20630-127 | 52U | 2450mm | 800mm | 1100mm | 1 | Black Grey |
| 20630-071 | 24U | 1200mm | 800mm | 600mm | 1 | Black Grey |
| 20630-261 | 42U | 2000mm | 600mm | 300mm | 1 | Black Grey |
| 20630-111 | 47U | 2200mm | 600mm | 600mm | 1 | Black Grey |
| 20630-115 | 47U | 2200mm | 600mm | 1100mm | 1 | Black Grey |
| 20630-113 | 47U | 2200mm | 600mm | 900mm | 1 | Black Grey |
| 20630-121 | 47U | 2200mm | 800mm | 1100mm | 1 | Black Grey |
| 20630-262 | 47U | 2200mm | 600mm | 300mm | 1 | Black Grey |
| 20630-116 | 47U | 2200mm | 600mm | 1200mm | 1 | Black Grey |
| 20630-103 | 42U | 2000mm | 600mm | 1100mm | 1 | Black Grey |
| 20630-099 | 42U | 2000mm | 600mm | 600mm | 1 | Black Grey |

Table 2/2

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|----------|-------------|
| 20630-118 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-067 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-091 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-120 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-084 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-126 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-092 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-119 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-125 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|----------|-------------|
| 20630-075 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-089 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-072 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-117 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-095 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-128 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-114 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-096 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-124 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-079 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-093 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-087 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-074 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-094 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-077 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-073 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-076 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-122 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-101 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-097 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-090 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-088 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-098 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-068 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-078 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-123 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-112 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-102 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-085 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-065 | RAL 7021 | | Steel | Standard | Varistar CP |

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|----------|-------------|
| 20630-110 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-083 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-105 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-109 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-082 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-106 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-100 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-086 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-107 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-066 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-104 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-080 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-108 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-081 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-127 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-071 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-261 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-111 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-115 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-113 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-121 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-262 | RAL 7021 | | Steel | Standard | Varistar CP |
| 20630-116 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-103 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-099 | RAL 7021 | | Steel | Standard | Varistar CP |

ADDITIONAL PRODUCT DETAILS

Castor can be added to the frame. If you will need a castor for your application, you can order a mobile frame which include castors.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE