

# Tray Handle

The tray handle can be clip into a cutout in the side panel of a case. 2 sizes available.



## CERTIFICATIONS



## FEATURES

Static load-carrying capacity 30 kg/pair

Side panel thickness min. 1,0 mm

## SPECIFICATIONS

|                        |   |
|------------------------|---|
| <b>Static Load:</b>    | 30kg  |
| <b>Color:</b>          | Black   |
| <b>Works With:</b>     | Cases   |
| <b>Product Family:</b> | RatiopacPRO; RatiopacPRO AIR; PropacPRO; CompacPRO; Comptec |
| <b>Product Type:</b>   | Handle  |
| <b>Material:</b>       | Polycarbonate   |
| <b>Type:</b>           | Static  |

Table 1/1

| Catalog Number | Height | Width | Depth | Package Quantity | Handle Type | Flammability Rating |
|----------------|--------|-------|-------|------------------|-------------|---------------------|
| 60225-012      | 79mm   | 187mm | 22mm  | 1                | Tray Handle | UL® 94V-0           |
| 60229-004      | 56mm   | 110mm | 18mm  | 1                | Tray Handle | UL® 94V-0           |

## ADDITIONAL PRODUCT DETAILS

---

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**