

Varistar CP Base/Plinth

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



FEATURES

2 support profiles, for front and rear

Static load-carrying capacity 1000 kg

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

Table 1/2

| Catalog Number | Height | Width | Package Quantity | Color | Color Code | Depth |
|----------------|--------|-------|------------------|------------|------------|-------|
| 24630-034 | 100mm | 600mm | 1 | Black Grey | RAL 7021 | 600mm |
| 24630-037 | 200mm | 800mm | 1 | Black Grey | RAL 7021 | |
| 24630-067 | 200mm | 800mm | 1 | Black Grey | RAL 7021 | |
| 24630-066 | 200mm | 600mm | 1 | Black Grey | RAL 7021 | |
| 24630-036 | 200mm | 600mm | 1 | Black Grey | RAL 7021 | |
| 24630-064 | 100mm | 600mm | 1 | Black Grey | RAL 7021 | |
| 24630-065 | 100mm | 800mm | 1 | Black Grey | RAL 7021 | |
| 24630-035 | 100mm | 800mm | 1 | Black Grey | RAL 7021 | |

Table 2/2

| Catalog Number | Finish | Type |
|----------------|---------------|-------------------------|
| 24630-034 | Powder Coated | Base Plinth, Perforated |
| 24630-037 | Powder Coated | Base Plinth, Perforated |

| Catalog Number | Finish | Type |
|----------------|---------------|-------------------------|
| 24630-067 | Powder Coated | Base Plinth, Plain |
| 24630-066 | Powder Coated | Base Plinth, Plain |
| 24630-036 | Powder Coated | Base Plinth, Perforated |
| 24630-064 | Powder Coated | Base Plinth, Plain |
| 24630-065 | Powder Coated | Base Plinth, Plain |
| 24630-035 | Powder Coated | Base Plinth, Perforated |

ADDITIONAL PRODUCT DETAILS

Please order side trims separately.

Cannot be used in conjunction with castors

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE