

# Varistar CP Deco Frame



The deco frame is a perfect fit for the Varistar CP without a front door. It conceals any cabling on the sides of the cabinet, streamlining cable routing and equipment mounting for a more efficient installation process and simultaneously improving the cabinet's appearance.

## FEATURES

Conceals cabling beside the 19" panel mount, streamlining cable routing and equipment mounting for a more efficient installation process

Provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs

Imparts improved functionality, appearance, and durability for Varistar CP cabinets without a door

Can be assembled at front and/or rear

## SPECIFICATIONS

- Static Load:** 400kgf
- Product Type:** Cabinet/Rack Frame
- Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Width | Design Feature       | Package Quantity | Color      |
|----------------|-------------|--------|-------|----------------------|------------------|------------|
| 21630-311      | 33U         | 1600mm | 600mm | 19" Plane Integrated | 1                | Black Grey |
| 21630-920      | 47U         | 2200mm | 800mm | Swing frame          | 1                | Black Grey |
| 21630-924      | 38U         | 1800mm | 800mm | 19" Slide Mounts     | 1                | Black Grey |
| 21630-309      | 24U         | 1200mm | 600mm | 19" Plane Integrated | 1                | Black Grey |
| 21630-314      | 47U         | 2200mm | 600mm | 19" Plane Integrated | 1                | Black Grey |

| Catalog Number | Rack Height | Height | Width | Design Feature       | Package Quantity | Color      |
|----------------|-------------|--------|-------|----------------------|------------------|------------|
| 21630-926      | 47U         | 2200mm | 800mm | 19" Slide Mounts     | 1                | Black Grey |
| 21630-919      | 42U         | 2000mm | 800mm | Swing frame          | 1                | Black Grey |
| 21630-313      | 42U         | 2000mm | 600mm | 19" Plane Integrated | 1                | Black Grey |
| 21630-310      | 29U         | 1400mm | 600mm | 19" Plane Integrated | 1                | Black Grey |
| 21630-918      | 38U         | 1800mm | 800mm | Swing frame          | 1                | Black Grey |
| 21630-925      | 42U         | 2000mm | 800mm | 19" Slide Mounts     | 1                | Black Grey |
| 21630-312      | 38U         | 1800mm | 600mm | 19" Plane Integrated | 1                | Black Grey |

Table 2/2

| Catalog Number | Color Code | Finish        | Type       |
|----------------|------------|---------------|------------|
| 21630-311      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-920      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-924      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-309      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-314      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-926      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-919      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-313      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-310      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-918      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-925      | RAL 7021   | Powder Coated | Deco Frame |
| 21630-312      | RAL 7021   | Powder Coated | Deco Frame |

## ADDITIONAL PRODUCT DETAILS

The deco frame provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs. It's an essential addition to any electronics cabinet without a front door, particularly for Automated Test Equipment, providing improved functionality, appearance, and durability.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**