

# AccessPlus Fan Kit

## Data Solutions



The AccessPlus Fan Kits are a four-inch, 115 VAC solution that provides air flow through cabinets at 100 CFM. The mounting plate and hardware is included. The small mounting plate is 5.32 (135 mm) x 8.00 (203 mm) and fits cabinets where C = 18.00. The large mounting plate is 5.32 (135 mm) x 10.75 (273 mm) and fits cabinets where C = 25.00 or 30.00.

### FEATURES

The AccessPlus Fan Kits are a four-inch, 115 VAC solution that provides air flow through cabinets at 100 CFM

The mounting plate and hardware is included

The small mounting plate is 5.32 (135 mm) x 8.00 (203 mm) and fits cabinets where C = 18.00

The large mounting plate is 5.32 (135 mm) x 10.75 (273 mm) and fits cabinets where C = 25.00 or 30.00

### SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Material | Finish        | Color     | Color Code | Thickness |
|----------------|----------------|----------|---------------|-----------|------------|-----------|
| EWMF1          | 17907          | Aluminum | Powder Coated | Jet Black | RAL 9005   | 2.5mm     |
| EWMF2          | 17908          | Aluminum | Powder Coated | Jet Black | RAL 9005   | 2.5mm     |

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**