We connect and protect

Basic PDU, EB0317-A, 230 VAC, 1-PH, 16 A

Data Solutions

CATALOG NUMBER

EB0317-A

Modular, compact PDU. Ultra-Low Profile Design

FEATURES

- Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures
- Input Voltage 230 VAC, 1-phase
- C13 and C19 outlets
- 1RU aluminum profile
- Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

- Product Family: Enlogic
- Type: Basic PDU
- Product Type: Socket Strip
- Socket Type: (10) C13; (1) C19
- Socket Quantity: 11
- Color: Black
- Circuit Breaker: 16 A, 1-pole, Hy-Mag
- Switched Outlets: No

Circuit Breaker Quantity: 0

Input Cable Location: Front Feed

Input Voltage: 100 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 3.68 kVA

Output Voltage: 100 – 240VAC

Amperage (Derated Amperage): 20 A (16 A) North America; 16 A International

Plug Type: C20

Rack Units: 0U

Removable Input Cable: Yes

Metering Type: None

Package Quantity: 1

Input Cable Length: 0m

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.