


Comptec GND/Earthing Kit



Protective GND/earthing connections in accordance with:
DIN EN 50178, VDE 0160 DIN EN 62368-1, VDE 0805 DIN EN
61010-1, VDE 0411 Part 1 DIN EN 61010-1A2, VDE 0411
Part 1/A1.

CERTIFICATIONS



FEATURES

Protective GND/earthing connections in accordance with: DIN EN 50178/VDE 0160 DIN EN 62368-1/VDE 0805
DIN EN 61010-1 /VDE 0411 Part 1 DIN EN 61010-1A2 /VDE 0411 Part 1/A1

VDE tested

SPECIFICATIONS

Product Family: Comptec
Type: Grounding Kit
Product Type: Grounding Kit

Table 1/1

Catalog Number	Package Quantity	Works With
21100-490	1	Cases, Steel Cover
21100-448	1	Cases, Steel Cover
21100-347	1	Cases, Aluminum Cover

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE