

# MTCA Guide Rail

Guide rail for MicroTCA.0, MicroTCA.1 and MicroTCA.4.



## CERTIFICATIONS



## FEATURES

Guide rail for MicroTCA.0, MicroTCA.1 and MicroTCA.4

Easy installation without tools in 1 HP grid; the minimum distance between two guide rails is 3 HP (compact)

## SPECIFICATIONS

Table 1/1

| Catalog Number | Type                  | Works With       | Material                   | Color  | Package Quantity |
|----------------|-----------------------|------------------|----------------------------|--------|------------------|
| 20849-198      | MicroTCA Carrier Hub  | MicroTCA Systems | Polybutylene Terephthalate | Grey   | 10               |
| 20849-202      | MicroTCA Carrier Hub  | MicroTCA Systems | Polybutylene Terephthalate | Grey   | 10               |
| 20849-194      | MicroTCA AdvancedMC   | MicroTCA Systems | Polybutylene Terephthalate | Red    | 10               |
| 20849-196      | MicroTCA Power Supply | MicroTCA Systems | Polybutylene Terephthalate | Yellow | 10               |
| 20849-200      | MicroTCA Universal    | MicroTCA Systems | Polybutylene Terephthalate | Green  | 10               |

| Catalog Number | Type                   | Works With       | Material                      | Color | Package Quantity |
|----------------|------------------------|------------------|-------------------------------|-------|------------------|
| 20849-201      | MicroTCA<br>Universal  | MicroTCA Systems | Polybutylene<br>Terephthalate | Green | 100              |
| 20849-195      | MicroTCA<br>AdvancedMC | MicroTCA Systems | Polybutylene<br>Terephthalate | Red   | 100              |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**