nVent CADDY

We connect and protect

nVent CADDY Superfix 243 M8, 25–30 mm OD, 3/4" Pipe, 20 DN

CATALOG NUMBER

SXE028

CERTIFICATIONS

FEATURES

- Includes easy closing mechanism
- Combo head bolt works with slotted, hex, or Phillips drivers
- Category II noise reduction according to DIN EN ISO 3822-1
- Compliant for sound insulation design according to DIN 4109
- Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

PRODUCT ATTRIBUTES

- Article Number: 400058
- Material: Steel;EPDM-SBR Rubber
- Finish: Electrogalvanized
- Color: Black
- Temperature: -50 to 110 °C

Outer Diameter (OD): 26 - 30 mm
Pipe Size: 3/4"
NB/DN: 20
Rod Size (RS): M8
Width (W): 20 mm
Thickness (T): 1.2 mm
Screw Diameter (Sc): 5
Screw Length (L): 25mm
Static Load: 1000N

ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.