

Compression Straight Lug, Standard, 300 mm² Stranded, 600 kcmil Stranded, 13 mm Hole

Data Solutions

CATALOG NUMBER

RKS050019H



FEATURES

Tin plated for corrosion prevention

Annealed copper eases the crimping operation

Optimized sizes to the most efficient electrical conductivity

Best mechanical behavior (vibration/pull-out); DIN EN 61373 Class 1B "Railway Applications"

Markings on barrel for crimping

Consistent material thickness, precise diameter and accurate cable fit; DIN46235

PRODUCT ATTRIBUTES

Article Number: 716546

Material: Copper

Finish: Tinned

Lug/Connector Type: Standard

Conductor Size: 300 mm² Stranded; 600 kcmil Stranded

Hole Size (HS): 13mm

Length (L): 109mm

Width (W): 43mm

Tool/Die Type: M2M or M2H/RKM2; M3H or M3B/RKM3

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE