We connect and protect

MSPO PDU, 0U, 60A(48A)NA/63A Int, 380-415V, 3P Wye, 12 CB, (18)C13, (18)4-in-1

Data Solutions

CATALOG NUMBER

EN6959

The Advantage Series Outlet Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at the input phase, circuit breaker, and individual outlet levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

FEATURES

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.
UL 2900-1 certified for safety software cybersecurity for network-connectable products.
Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address
Ethernet cascading up to 64 PDUs
Each PDU can provide DC power sufficient to power network management electronics
Dual Ethernet ports for redundant network connunications
Remote connectivity through HTTP(s), iPV4 and iPV6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)
Data efficient REACT framework with native mobile device support
Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs
The border color of the NMC display is user programmable for power source identification by PDU
The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring
Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

PRODUCT ATTRIBUTES

Product Family: Enlogic
Type: Intelligent PDU
Product Type: Socket Strip
Socket Type: (18) C13/C15; (18) C13/C15/C19/C21
Socket Quantity: 36
Color: Black
Switched Outlets: Yes
Power Rating: 34.6 kVA North America; 43.5 kVA International
Cable Length: 1800mm
Circuit Breaker: 20 A, 1-pole, Hy-MagA
Circuit Breaker Quantity: 12
Nominal Voltage: 415V
Nominal Power Output: 230VAC
Number of Output Voltages: 36
Amperage (Derated Amperage): 60 A (48 A) North America; 63 A International
Rack Units: 0U
On/Off Switch Included: Yes
Output Voltage: 208 – 230VAC
Metering Type: Outlet
Plug Type: IEC 60309 560P6/563P6
Removable Input Cable: No
Material: Steel
Finish: Powder Coated
Height: 1720mm
Width: 56mm
Depth: 75mm
Package Quantity: 1
Input Cable Length: 1.8m

ADDITIONAL PRODUCT DETAILS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.