


# Open Frame Panel Adapter



The Open-Frame Panel Adapter adapts a 23-inch open-frame rack to accept 19-inch equipment. The offset provides a flush mounting surface. Please note these are furnished in pairs.

## FEATURES

---

The Open-Frame Panel Adapter adapts a 23-inch open-frame rack to accept 19-inch equipment

The offset provides a flush mounting surface

Please note these are furnished in pairs

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Thickness	Rack Units
ERB1U2319	21939	Mild Steel	Zinc Plated	1.9mm	1U
ERB3U2319	21949	Mild Steel	Zinc Plated	1.9mm	3U
ERB5U2319	21959	Mild Steel	Zinc Plated	1.9mm	5U

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**